

1 LABORATORY - NEW PLUMBING IN CRAWL SPACE

## KEY NOTES

- 1) NEW FLOOR DRAINS C/W NEW TRAPS TO REPLACE EXISTING, TO SUIT FLOOR FINISH; SEE SPECIFICATIONS FOR DETAILS.
- $\left\langle 2 \right\rangle$  NEW COMBINATION DELUGE SHOWER/EYE WASH, SEE ARCHITECTURAL
- 4 130 DCW & DHW TO SINK FROM WORK BENCH CHASE, C/W ISOLATION VALVES
- $\left\langle 5 \right\rangle$  NEW 130 DI WATER LINE TO DI FAUCET FROM WORK BENCH PIPE CHASE.
- $\fbox{6}$  130 DI WATER TO CUP SINK WITHIN BASE CABINET CHASE, C/W ISOLATION VALVE
- 7 ) 130 CA TO CA BIB, C/W ISOLATION VALVE UNDER COUNTER C/W ISOLATION VALVE.
- 8 130 VACUUM TO VACUUM BIB, C/W ISOLATION VALVE UNDER COUNTER.
- NEW 13# PROCESS & DOMESTIC LINES TO WORK BENCH PIPE CHASE; LINES AS FOLLOWS:
  -13# DOW
  -13# DOW
  -13# DO HW
  -13# DO HW
  -13# DO H

- CORE NEW FLOOR OPENINGS, TO SUIT; ALL LINES WILL BE C/W ISOLATION VALVES ABOVE FLOOR PIPE PENETRATIONS TO MATCH FLOOR RATING; LINES TIGHT TO BLOCK WALL WITHIN NEW FURRING
- 10) NRW 13a PROCESS & DOMESTIC LINES TO FUNE HOOD; LINES AS FOLLOWS:

  -13b DHW

  -13b DHW

  -13b CA

  -13b CA

  -13b CAULUM

- -138 VACUUM
  CORE NEW FLOOR OPENINGS, TO SUIT; ALL LINES WILL BE C/W ISOLATION VALVES ABOVE FLOOR
  PIPE PENETRATIONS TO MATCH FLOOR RATING; LINES TIGHT TO BLOCK WALL WITHIN NEW FURRING
- 11) 32¢ DTW (DOMESTIC TEMPERED WATER) FROM BASEMENT, THRU NEW WALL FURRING; PROVIDE ISOLATION VAVE ABOVE FLOOR; PIPE PENETRATION TO MATCH FLOOR RATING
- $\fbox{12}$  320 PROCESS DRAIN LINE FROM ES-1 COLUMN (EYEWASH DRAIN), THRU FLOOR TO NEW ROOM PROCESS DRAIN
- 389 PROCESS DRAIN LINE, RUN INSIDE FUNE HOOD BASE CABINET THRU FLOOR TO CRAINL SPACE, CONNECT TO NEW 759 PROCESS DRAIN MAIN, TO SERVICE SINK AND CUP SINK; RUN 389 VENT UI INTO CEILING SPACE; CONNECT TO NEW COMMON 759 VENT THRU ROOF
- (15) NEW 750 VENT STACK TO SERVICE ALL VENTED FIXTURES IN NEW LAB; PROVIDE NEW PITCH POCKET AND EXTEND THRU ROOF; INCREASE PIPE SIZE TO 1000 BELOW ROOF; TERMINATE 150mm ABOVE PITCH POCKET

## KEY NOTES

- 1 NEW 750 PROCESS DRAIN FROM NEW FLOOR DRAIN, C/W TRAP & TRAP PRIMER
- 2) NEW 750 PROCESS DRAIN; SLOPE DN. 1%; SUPPORT LINE WITH PIPE HANGERS FROM FLOOR ABOVE; PROVIDE IN LINE CLEANOUTS AT ALL CHANGES IN DIRECTION.
- 3 CONNECT NEW 75¢ PROCESS DRAIN TO EXISTING PROCESS DRAIN STACK
- 4 380 DELUGE SHOWER/EYEWASH DRAIN, SLOPE DN 1%
- 5 380 DISWASHER DRAIN; SLOPE DN. 1%
- 6 38¢ WORK FUME HOOD DRAIN LINE; SLOPE DN 1%
- $\overline{7}$  380 BENCH DRAIN LINE; SLOPE DN 1%
- 8 CORE OPENING TO SUIT NEW PROCESS DRAIN OD
- NEW 136 PROCESS & DOMESTIC LINES TO WORK BENCH PIPE CHASE; LINES AS FOLLOWS:

  136 DOW

  136 DOW

  136 DOW


  136 DOW

  136 DOW

  136 DOW

  138 DO
- CORE NEW FLOOR OPENINGS, TO SUIT; ALL LINES WILL BE C/W ISOLATION VALVES ABOVE FLOOR PIPE PENETRATIONS TO MATCH FLOOR RATING; LINES TIGHT TO BLOCK WALL WITHIN NEW FURRING
- 11) 320 DTW (DOMESTIC TEMPERED WATER) TO NEW LAB, THRU WALL FURRING; PIPE PENETRATION TO MATCH FLOOR FIRE RATING
- (12) 32# PROCESS DRAIN LINE FROM ES-1 COLUMN (EYEWASH DRAIN), NEW LAB ABOVE TO NEW LAB PROCESS DRAIN MAIN; SLOPE DN. 1%

## ALLIANCEEngineering Services Inc.






M2.1

THE CITY OF WINNIPEG WATER AND WASTE DEPARTMENT Winnipèg

ORTH END WATER POLLUTION CONTROL CENTRE LAB RENOVATIONS

CONSULTANT DRAWING NO. PLUMBING MODIFICATIONS PLANS

1-0101M-H0003-001-01



## GENERAL NOTES

- 1. PERFORM ALL WORK IN ACCORDANCE WITH ALL APPLICABLE CODES, STANDARDS AND CITY INSPECTIONS REQUIREMENTS.
- Coordinate works with other sub-trades. Refer to specific details for cutting and sealing penetrations through openings & fire separations.
   Refer to specific details for cutting and sealing penetrations are to technical septications for equipment and material specifications and installation and construction requirements.
- INSULATE PLUMBING PIPES AND DUCTWORK WHERE INDICATED AND AS SPECIFIED.
- INSULIE PLUMBING LINES AND DUCTHORS TO DEET CODE REQUIRELEMENTS & ESTABLISHED INDUSTRY TRADE PRACTICES, (SMACNA, ASHRAE).

  MINESTIGATE SITE PRORE TO CONSTRUCTION TO CONFIRM ALL DIMENSIONS AND INSTALLATION REQ'S.

  PERFORM ALL CUTTING & PATCHING NECESSARY FOR ANY REQUIRED OPENINGS THRU WALLS, ROOF AND FLOOR.
- PROVIDE TAB TO ENSURE AIR DISTRIBUTION TO VOLUMES INDICATED.
- NOT ALL EQUIPMENT/PIPING, ETC. IS SHOWN.
   ROYUNG FIRE STOPS AT ALL FIRE RATED WALLS/FLOOR DENNINGS TO MATCH EXISTING RATING
   LAL PROCESS DWY TO BE AGD RESISTANT, CPVL, SEE SPECIFICATIONS.
   ALL DI WATER SUPPLY TUBING TO BE SCH. 80 CPVC, SEE SPECIFICATIONS.

- CHECK SHOP DRAWINGS FOR ALL NEW LAB PLUMBING FIXTURES, TO CONFIRM NUMBER AND SIZE OF FITTINGS SUPPLIED, FIXTURE STOPS, BY LAB EQUIPMENT SUPPLIER AND CONNECTION SIZE FOR ALL SERVICES TO FIXTURES.
- 14. NOTE: WHERE ISOLATION VALVES ARE REQUESTED ON PIXTURE WATER SUPPLIES, THESE VALVES ARE OVER AND ABOVE ANY PIXTURE STOPS PROVIDED BY THE LAB EQUIPMENT SUPPLIER.